


# WDESK-G

WEIGHT INDICATOR - WEIGHING AND BATCHING

LAUMAS®



MULTILINGUAL  
 SOFTWARE



Indicator-holder bracket and column  
 Stainless steel bracket for wall mounting  
 Panel mounting

## PROGRAM

## CODE

|               |           |
|---------------|-----------|
| BASE          | WDESKG-B  |
| LOAD          | WDESKG-C  |
| UNLOAD        | WDESKG-S  |
| 3 PRODUCTS    | WDESKG-3  |
| * 6 PRODUCTS  | WDESKG-6  |
| * 14 PRODUCTS | WDESKG-14 |
| Multiprogram  | WDESKG-MU |

\* External 8-relay modules included

## CERTIFICATIONS

- OIML R76:2006, class III, 3x10000 divisions, 0.2  $\mu$ V/VSI / OIML R61 - WELMEC Guide 8.8:2011 (MID)
- UL Recognized component - Complies with United States and Canada standards
- Complies with the Eurasian Customs Union standards
- Equivalent of the CE marking for the United Kingdom
- NMI Trade Approved - Complies with Australian market regulations for legal for trade use
- Complies with New Zealand regulations for legal for trade use
- Complies with United Kingdom regulations for legal for trade use
- NTEP -  $n_{max}$  10000 - Class III/IIIL - Complies with United States regulations for legal for trade use

### CERTIFICATIONS ON REQUEST

|          |                                                                                               |
|----------|-----------------------------------------------------------------------------------------------|
| <b>M</b> | Conformity assessment (initial verification) in combination with Laumas weighing module (   ) |
|          | Complies with the regulations of the Russian Federation for legal for trade use               |

## FIELDBUSES



### DESCRIPTION

- ABS weight indicator.
- Backlit LCD graphic display, resolution: 240x64 pixel, visible area: 133x39 mm.
- 21-key keyboard.
- Real-time clock/calendar with buffer battery.
- Multilanguage software (4 languages + 1 customizable).

*To know the specific characteristics of the various instrument versions, refer to the table of available versions.*

### MAIN FUNCTIONS

- Connections to:
  - PLC via analog output (on request);
  - PC/PLC via RS485/RS232 (up to 99 instruments with line repeaters, up to 32 without line repeaters);
  - remote display and printer via RS485/RS232;
  - up to 8 load cells in parallel by junction box.
  - IoT gateway for cloud connection via RS485.
- TCP/IP WEB APP: integrated software in combination with the WiFi module and Ethernet TCP/IP options for remote supervision, management and control of the instrument.
- Customizable name of the production lot.
- Digital filter to reduce the effects of weight oscillation.
- Theoretical calibration (via keyboard) and real calibration (with sample weights and the possibility of weight linearization up to 8 points).
- Tare weight zero setting.
- Automatic zero setting at power-on.
- Gross weight zero tracking.
- Semi-automatic tare (net/gross weight) and preset tare.
- Semi-automatic zero.
- Displaying of the maximum weight value reached (peak).
- Direct connection between RS485 and RS232 without converter.
- Weight value printing with date and time via keyboard or external contact.

#### Approved versions for legal for trade use

- System parameters management protected by qualified access via software (password), hardware or fieldbus.
- Weight subdivisions displaying (1/10 e).
- Three operation mode: single interval or multiple ranges or multi-interval.
- Net weight zero tracking.
- Calibration.
- Alibi memory (option on request).
- The following values can be printed via keyboard or external contact: gross weight, net weight, tare, preset tare, date, time, ID code (alibi memory).

### INPUTS/OUTPUTS AND COMMUNICATION

- RS485/RS232 serial ports for communication via protocols ModBus RTU, ASCII Laumas or continuous one way transmission.
- 5 relay outputs controlled by the setpoint values or via protocols (4 outputs if analog output is present).
- 3 optoisolated PNP digital inputs: status reading via serial communication protocols (2 inputs if analog output is present).
- 1 load cell dedicated input.
- Current or voltage 16 bit optoisolated analog output (option on request).
- WiFi module (option on request).

### BASE PROGRAM

- Piece counting.
- Weight totalizing.
- Statistical checking of prepackages.
- 99 items database with association of a preset tare value, 3 setpoint values and 2 values for weight thresholds function (HIGH/LOW).
- Weight thresholds function (HIGH/LOW) shown on the display.
- Barcodes printing by lot name, item name, weighings progressive number.
- Hysteresis and setpoint value setting.
- The indicator can be used as a remote display with setpoints.
- 12 groups selection by 5 setpoint via external selector switch or contact (option on request).

### BATCHING PROGRAM

- Graphical representation of the system load status.
- 99 settable formulas.
- Batching resume after a blackout.
- Automatic fall calculation.
- Tolerance error control.
- Precision batching through slow function.
- Precision batching through tapping function.
- Consumption storage.
- Production storage.
- Products stocks management.
- Printing of batching data.
- Alarm contact management.
- Selection of the first 12 formulas via external selector switch or contact (option on request).
- Batching start via external contact or keyboard.

*Only for:*

LOAD and 3/6/14 PRODUCTS programs

- Autotare at batching start.

UNLOAD program

- Automatic loading of the product into the weighed structure.
- Management of batching with big bags.

3/6/14 PRODUCTS program

- Formulas programming in fixed or variable steps.

### MULTIPROGRAM

- The Multiprogram instruments do not have any selected program but can be set by the installer with different operating modes: BASE, LOAD, UNLOAD, 3 PRODUCTS, 6 PRODUCTS, 14 PRODUCTS.

### TECHNICAL FEATURES

|                                                                  |                                                                                                    |
|------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|
| Power supply and consumption                                     | 12÷24 VDC ±10%; 6 W (on request: 115÷230 VAC; 50÷60 Hz; 6 VA)                                      |
| Number of load cells • Load cells supply                         | up to 8 (350 Ω) - 4/6 wires • 5 VDC/120 mA                                                         |
| Linearity • Analog output linearity                              | <0.01% full scale • <0.01% full scale                                                              |
| Thermal drift • Analog output thermal drift                      | <0.0005% full scale/°C • <0.003% full scale/°C                                                     |
| A/D Converter                                                    | 24 bit (16000000 points) - 4.8 kHz                                                                 |
| Divisions (with measurement range ±10 mV and sensitivity 2 mV/V) | ±999999 • 0.01 μV/d                                                                                |
| Measurement range                                                | ±39 mV                                                                                             |
| Usable load cells sensitivity                                    | ±7 mV/V                                                                                            |
| Conversions per second                                           | 300/s                                                                                              |
| Display range                                                    | ±999999                                                                                            |
| Decimals • Display increments                                    | 0÷4 • x1 x2 x5 x10 x20 x50 x100                                                                    |
| Digital filter • Readings per second                             | 10 levels • 5÷300 Hz                                                                               |
| Relay outputs                                                    | 5/4 - max 115 VAC/150 mA                                                                           |
| Optoisolated digital inputs                                      | 3/2 - 5÷24 VDC PNP                                                                                 |
| Serial ports                                                     | RS485, RS232                                                                                       |
| Baud rate                                                        | 2400, 4800, 9600, 19200, 38400, 115200 (bit/s)                                                     |
| Optoisolated analog output (option on request)                   | 16 bit = 65535 divisions. 0÷20 mA; 4÷20 mA (up to 300 Ω)<br>0÷10 V; 0÷5 V; ±10 V; ±5 V (min 10 kΩ) |
| Humidity (condensate free)                                       | 85%                                                                                                |
| Storage temperature                                              | -30 °C +80 °C                                                                                      |
| Working temperature                                              | -20 °C +60 °C                                                                                      |

|                                                                                     |                                                                  |                                 |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------|---------------------------------|
|  | Relay outputs                                                    | 5/4 - max 30 VAC, 60 VDC/150 mA |
|                                                                                     | Working temperature                                              | -20 °C +50 °C                   |
|                                                                                     | Equipment to be powered by 12-24 VDC LPS or Class 2 power source |                                 |

| METROLOGICAL SPECIFICATIONS OF<br>TYPE-APPROVED INSTRUMENTS | OIML                                                                                                                                                                                                                                                                    | NTEP                                              |
|-------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|
| Applied standards by region                                 | EU: 2014/31/UE; OIML R76:2006; EN45501:2015<br>Russian Federation: GOST OIML R76-1-2011<br>United Kingdom: Non-automatic Weighing Instrument Regulations 2016<br>Australia: National Measurement Regulations 1999<br>New Zealand: Weights and Measures Regulations 1999 | USA: NIST HANDBOOK 44, 2020;<br>NCWM PUB 14, 2021 |
| Operation modes                                             | single interval, multi-interval, multiple range                                                                                                                                                                                                                         | single interval, multi-interval, multiple range   |
| Accuracy class                                              | III or IIIL                                                                                                                                                                                                                                                             | III or IIIL                                       |
| Maximum number of scale verification divisions              | 10000 (class III); 1000 (class IIIL)                                                                                                                                                                                                                                    | 10000 (class III/IIIL)                            |
| Minimum input signal for scale verification division        | 0.2 μV/VSI                                                                                                                                                                                                                                                              |                                                   |
| Working temperature                                         | -10 °C +40 °C                                                                                                                                                                                                                                                           | -10 °C +40 °C (+14 °F +104 °F)                    |

### Example screens for BASE program

#### Piece counter

|   |          |                    |
|---|----------|--------------------|
| 1 | NAME:    | BOLT               |
| 2 | TARE:    | 12 kg              |
| 3 | TOTAL:   | 19691 kg           |
| 4 | NUM:     | 6                  |
| 5 | TOT PCS: | 357                |
|   | PCS:     | 65                 |
|   |          | 3602 [NET] [ ] [ ] |

1. Totalized weight since last deletion.
2. Performed weighings since last deletion.
3. Totalized pieces since last deletion.
4. Number of pieces.
5. Net weight.

#### Totalizer

|   |        |                    |
|---|--------|--------------------|
| 1 | NAME:  | FLOUR              |
| 2 | TARE:  | 5 kg               |
| 3 | GROSS: | 1382 kg            |
| 4 | DATE:  | 04/07/13           |
|   | NUM:   | 5                  |
|   | TOT:   | 4974               |
|   |        | 1377 [NET] [ ] [ ] |

1. Date of last deletion.
2. Performed weighings since last deletion.
3. Totalized weight since last deletion.
4. Net weight.

#### Statistical checking of prepackages

|   |         |                          |
|---|---------|--------------------------|
| 1 | LOT:    | LOT-000015               |
| 2 | NAME:   | FLOUR 1KG                |
| 3 | TARGET: | 1.000 kg                 |
| 4 | TARE:   | 0.010 kg                 |
|   | NUM:    | 9 / 30                   |
|   |         | [21] [22] [23] [24] [25] |
|   |         | 1.004 [NET] [ ] [ ]      |

1. Nominal weight.
2. Checked samples/total samples.
3. Tolerance zone.
4. Net weight.

#### Production displaying for each formula (amount of batched product and number of cycles performed)

|   |                    |
|---|--------------------|
| 1 | PRODUCTION FOR: 01 |
|   | 05/07/2013 09:59   |
| 2 |                    |
|   | FOR QTY CYCLE      |
|   | 1 4587 0002        |
|   | 2 0 0000           |
|   | 3 0 0000           |
|   | 14 [ ] [ ] [ ]     |

1. Date and time of last deletion.
2. Formulas list.
3. Selected formula.
4. Batched quantity and number of cycles performed.

#### Consumptions displaying for each product 3/6/14 PRODUCTS program

|   |                  |                |
|---|------------------|----------------|
| 1 | TOT:             | 4587 kg        |
|   | PR: 01           |                |
|   | 05/07/2013 09:59 |                |
| 2 |                  |                |
|   | PR QTY           |                |
|   | 1 990            |                |
|   | 2 1056           |                |
|   | 3 1145           |                |
|   |                  | 13 [ ] [ ] [ ] |

1. Date and time of last deletion.
2. Products list.
3. Selected product.
4. Consumptions.

### Example screens for BATCHING programs

#### Formulas programming 3/6/14 PRODUCTS program

|   |               |                   |
|---|---------------|-------------------|
| 1 | FORMULA:      | 01                |
|   | STEP PROD SET |                   |
|   | 01 01 400     |                   |
|   | 02 02 500     |                   |
|   | 03 03 500     |                   |
|   | 04 04 600     |                   |
|   | FOR PO 1      |                   |
|   |               | [NET] [ ] [ ] [ ] |

1. Selected formula.
2. Step number.
3. Product number.
4. Set value.

#### Formulas programming LOAD and UNLOAD programs

|   |                 |                   |
|---|-----------------|-------------------|
| 1 | FORM PRESET SET |                   |
|   | 01 900 1000     |                   |
|   | 02 0 0          |                   |
|   | 03 0 0          |                   |
|   | 04 0 0          |                   |
|   | FOR PO 1        |                   |
|   |                 | [NET] [ ] [ ] [ ] |

1. Selected formula.
2. Preset value.
3. Set value.

#### Details of batching product displaying LOAD and UNLOAD programs

|   |            |                   |
|---|------------|-------------------|
| 1 | FORMULA:   | 01                |
| 3 | CYCLE:     | 1/1               |
| 5 | PROD:      | 01                |
|   | PRESET:    | 900               |
|   | SET:       | 1000              |
| 7 | FALL:      | 0                 |
|   | TOLERANCE: | 0                 |
|   |            | b 349 [ ] [ ] [ ] |

1. Formula number.
2. Running cycle.
3. Product number.
4. Preset value.
5. Set value.
6. Fall value.
7. Tolerance value.

#### Displaying during the batching 3/6/14 PRODUCTS program

|   |    |                   |
|---|----|-------------------|
| 1 | 04 | FORMULA: 01       |
|   | ↓  | CYC: 1/1          |
|   |    | PO4: GRAIN        |
|   |    | SET: 600          |
| 2 |    | K9 BATCHING       |
|   |    | 1990              |
|   |    | b 358 [ ] [ ] [ ] |

1. Product number and arrow indicating the product loading.
2. Product level on the scale.
3. Formula number.
4. Running cycle.
5. Product number and name.
6. Gross weight value.
7. Batching product weight.

#### Stocks displaying for each product 3/6/14 PRODUCTS program

|   |                  |                |
|---|------------------|----------------|
| 1 | STOCKS           | PR: 01         |
|   | 05/07/2013 10:04 |                |
| 2 |                  |                |
|   | PR QTY           |                |
|   | 1 19010          |                |
|   | 2 18944          |                |
|   | 3 18855          |                |
|   |                  | 14 [ ] [ ] [ ] |

1. Current date and time.
2. Products list.
3. Selected product.
4. Stocks.

# WDESK-G

## WEIGHT INDICATOR - WEIGHING AND BATCHING

LAUMAS®

### AVAILABLE VERSIONS

|                                                                                     | DESCRIPTION                                                                                                                                                                                                                                                                                                                                                                                  | CODE    |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
|    | <b>P version (standard)</b> <ul style="list-style-type: none"> <li>- Installation: desk, wall, column, front panel (drilling template: 186x96 mm).</li> <li>- Dimensions: 226x122x164 mm.</li> <li>- IP67 protection rating.</li> <li>- 6 M16x1.5 cable glands.</li> <li>- Power supply included: 24 VDC/1 A - 100÷240 VAC input cable length: 3 m.</li> </ul>                               | WDESK-P |
|    | <b>Q version</b> <ul style="list-style-type: none"> <li>- Installation: front panel (supports included; drilling template: 186x92 mm), desk, wall.</li> <li>- Dimensions: 226x122x152 mm.</li> <li>- IP67 front panel protection rating.</li> <li>- Removable screw terminal blocks.</li> </ul>                                                                                              | WDESK-Q |
|   | <b>D version</b> <ul style="list-style-type: none"> <li>- Installation: desk, wall, column, front panel (drilling template: 186x96 mm).</li> <li>- Dimensions: 226x122x189 mm.</li> <li>- IP40 protection rating.</li> <li>- IP67 front panel protection rating.</li> <li>- D-SUB connectors.</li> <li>- Power supply included: 24 VDC/1 A - 100÷240 VAC input cable length: 3 m.</li> </ul> | WDESK-D |
|  | <b>X version: ATEX II 3GD (zone 2-22) (CE UK CA)</b> <ul style="list-style-type: none"> <li>- Installation: desk, wall, column, front panel (drilling template: 186x96 mm).</li> <li>- Dimensions: 226x122x164 mm.</li> <li>- IP67 protection rating.</li> <li>- 6 M16x1.5 cable glands.</li> </ul>                                                                                          | WDESK-X |

### OPTIONS ON REQUEST

|                                                                                     | ACCESSORIES                                                                                                              | CODE                   |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|------------------------|
|  | Stainless steel adjustable bracket for wall and table mounting.<br>Dimensions with bracket: 230x122x250 mm.              | STAFFAINOXWDESK        |
|  | Supports for front panel mounting.                                                                                       | STAFFEWINOX            |
|  | ABS adjustable support for column mounting.                                                                              | STAFFAWDESK            |
|  | Stainless steel indicator-holder column (Ø38 mm, height 700 mm).<br>Painted steel bracket for platform/floor mounting.   | COLONNAM<br>+ STAFFACN |
|                                                                                     | Stainless steel indicator-holder column (Ø38 mm, height 700 mm).<br>Stainless steel bracket for platform/floor mounting. | COLONNAM<br>+ STAFFAIN |

### OPTIONS ON REQUEST


|                                                                                    | POWER SUPPLY                                                                                                                                                        | CODE              |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
|   | Power supply 115/230 VAC; 50/60 Hz; 6 VA.<br>➔ <i>Not compatible with D version.</i><br>➔ <i>Not compatible with EAC certifications.</i>                            |                   |
|   | 24 VDC/1 A stabilized power supply.<br>- 100÷240 VAC input.<br>- 3 m cable length.                                                                                  | ALI24SPINA1A      |
|   | 24 VDC/1 A stabilized power supply with jack connector.<br>- 100÷240 VAC input.<br>- 3 m cable length.                                                              | ALI24SPINA1AJACK  |
|   | 24 VDC/1 A stabilized power supply with omega rail socket.<br>- 100÷240 VAC input.<br>- 3 m cable length, with or without jack connector.                           | ALI24SPINAPRESA   |
|   | Battery pack made up of 8 NiMH rechargeable elements, 1.2 V, AA type.<br>- Non-removable.<br>- Operating time: 16 hours.<br>➔ <i>Not compatible with X version.</i> | OPZWBATTWDESK     |
|  | Battery pack made up of 8 NiMH rechargeable elements, 1.2 V, AA type.<br>- Non-removable.<br>- Operating time: 16 hours.                                            | OPZWBATTWDESKATEX |

### OPTIONS ON REQUEST AND COMPATIBILITY WITH BATCHING PROGRAMS



| INTERFACES AND FIELDBUSES                                                           |                                                                                                                                                                                                                                                                                       | CODE                                                                 |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------|
|    | <b>WiFi module</b> (2.4 GHz) for wireless connection via integrated web server (for remote supervision, management and control of the instrument) or via ModBus RTU, ASCII Laumas protocols.<br>(* for Q version)<br>➔ X version: only available with internal antenna.               | * OPZW1RADIO<br>* OPZW1RADIOQ(*)<br>B C S 3P 6P 14P<br>• • • • • •   |
|    | <b>Optoisolated 16 bit analog output.</b><br>➔ One input and one output not available.                                                                                                                                                                                                | * OPZW1ANALOGICA<br>B C S 3P 6P 14P<br>• • • • • •                   |
|    | <b>Additional RS485 port.</b><br>➔ One input and one output not available.<br>➔ Not compatible with E/EC option.                                                                                                                                                                      | * OPZW1RS485<br>B C S 3P 6P 14P<br>• • • • • •                       |
|    | <b>CANopen protocol.</b><br>➔ Q version: one input and one output not available.<br>➔ Q version: integrated RS485 port not available.<br>➔ Q, P, X version: not compatible with E/EC option.                                                                                          | * OPZW1CA<br>B C S 3P 6P 14P<br>• - - - - -                          |
|    | <b>DeviceNet protocol.</b><br>➔ Q version: one input and one output not available.<br>➔ Q version: integrated RS485 port not available.<br>➔ Q, P, X version: not compatible with E/EC option.                                                                                        | * OPZW1DE<br>B C S 3P 6P 14P<br>• - - - - -                          |
|   | <b>Profibus DP protocol.</b><br>➔ Q version: one input and one output not available.<br>➔ Q version: integrated RS485 port not available.<br>➔ Q, P, X version: not compatible with E/EC option.                                                                                      | * OPZW1PR<br>B C S 3P 6P 14P<br>• • • • • •                          |
|  | <b>Ethernet/IP protocol - IP68 Ethernet port.</b><br>➔ X, P version: internal crimp wiring.                                                                                                                                                                                           | * OPZW1ETIP68<br>* OPZW1ETIPCR<br>B C S 3P 6P 14P<br>• - - - - -     |
|  | <b>Ethernet TCP/IP protocol - IP68 Ethernet port.</b><br>Integrated software for remote supervision, management and control of the instrument.<br>➔ X, P version: internal crimp wiring.                                                                                              | * OPZW1ETTCP68<br>* OPZW1ETTCCPCR<br>B C S 3P 6P 14P<br>• • • • • •  |
|  | <b>Modbus/TCP protocol - IP68 Ethernet port.</b><br>➔ X, P version: internal crimp wiring.                                                                                                                                                                                            | * OPZW1MBTCP68<br>* OPZW1MBTCPCR<br>B C S 3P 6P 14P<br>• • • • • •   |
|  | <b>Profinet IO protocol - IP68 Ethernet port.</b><br>➔ X, P version: internal crimp wiring.                                                                                                                                                                                           | * OPZW1PNETIO68<br>* OPZW1PNETIOCR<br>B C S 3P 6P 14P<br>• - - - - - |
|  | <b>IP68 USB port</b> for data storage to pen drive (included). These data (weighed values, batchings, alarms) can be imported and processed on the PC using the PROG-DB software included in the supply. Support for keyboard and barcode reader.<br>➔ Not compatible with X version. | OPZWUSB68<br>B C S 3P 6P 14P<br>• • • • • •                          |
|  | <b>USB port</b> for data storage to pen drive (included). These data (weighed values, alarms) can be imported and processed on the PC using the PROG-DB software included in the supply.<br>➔ Not compatible with X version.                                                          | OPZWUSBDB9<br>B C S 3P 6P 14P<br>• • • • • •                         |

\* Select one option among those marked with an asterisk.

### OPTIONS ON REQUEST AND COMPATIBILITY WITH BATCHING PROGRAMS

|                                                                                     |                                                                                                                    | CODE                                            |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|
|    | Extension cable for the WiFi module antenna; length: 100 cm.<br>→ Q version: included with the OPZW1RADIOQ option. | OPZWCONWF<br>B C S 3P 6P 14P<br>• • • • •       |
|    | USB male/female extension cable with IP68 panel connector; length: 50 cm, sealing cap and cover included.          | OPZWCONUSBIP68<br>B C S 3P 6P 14P<br>• • • • •  |
|    | Ethernet male/female extension cable with IP68 panel connector; length: 30 cm, sealing cap included.               | OPZWCONETHEIP68<br>B C S 3P 6P 14P<br>• • • • • |
|    | Ethernet male/male extension cable with IP68 connector; length: 5 m.                                               | OPZWCONETHE5MT<br>B C S 3P 6P 14P<br>• • • • •  |
|   | Weight reading from 0-10 VDC input (15 kΩ).<br>→ Not compatible with X version.                                    | OPZWING010<br>B C S 3P 6P 14P<br>• • • • •      |
|  | Weight reading from 4-20 mA input (120 Ω).<br>→ Not compatible with X version.                                     | OPZWING420<br>B C S 3P 6P 14P<br>• • • • •      |

### EXPANSIONS

|                                                                                     |                                                                                                                                                                          |                                          |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------|
|  | Base: 12 groups selection by 5 setpoint via external selector switch.<br>Load, Unload, 3/6/14 Products: selection of the first 12 formulas via external selector switch. | * EC<br>B C S 3P 6P 14P<br>• • • • •     |
|  | Base: 12 groups selection by 5 setpoint via external contact.<br>Load, Unload, 3/6/14 Products: selection of the first 12 formulas via external contact.                 | * E<br>B C S 3P 6P 14P<br>• • • • •      |
|  | Simultaneous use of E/EC option with the analog output.                                                                                                                  | OPZWAEC<br>B C S 3P 6P 14P<br>• • • • •  |
|  | External 5-relay module to increase the capacity of SPDT contacts to 115 VAC/2 A.                                                                                        | RELE5M<br>B C S 3P 6P 14P<br>• • • • - - |

\* Select one option among those marked with an asterisk.

### OPTIONS ON REQUEST AND COMPATIBILITY WITH BATCHING PROGRAMS

|                                                                                   |                                                                                                                                                                     |             | CODE          |   |   |    |    |     |
|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|---------------|---|---|----|----|-----|
|  | External 8-relay module to manage from 1 to 6 products; 8 relays up to max 115 VAC/2 A.<br>Module included with models 6/14 PRODUCTS.                               | 12÷24 VDC   | RELE6PROD24V  |   |   |    |    |     |
|                                                                                   |                                                                                                                                                                     | 115/230 VAC | RELE6PROD230V |   |   |    |    |     |
|                                                                                   |                                                                                                                                                                     |             | B             | C | S | 3P | 6P | 14P |
|                                                                                   |                                                                                                                                                                     |             | —             | — | — | —  | •  | •   |
|  | External 8-relay module to manage from 7 to 14 products to be added to RELE6PROD module; 8 relays up to max 115 VAC/2 A.<br>Module included with model 14 PRODUCTS. |             | RELE14PROD    |   |   |    |    |     |
|                                                                                   |                                                                                                                                                                     |             | B             | C | S | 3P | 6P | 14P |
|                                                                                   |                                                                                                                                                                     |             | —             | — | — | —  | —  | •   |

### APPLICATIONS - SOFTWARE

|                                                                                     |                                                                                                                                                                                                                                                                                                                    |                 |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
|    | Formulas setting in percentage.                                                                                                                                                                                                                                                                                    | OPZWFORPERC     |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | — — — • • •     |
|    | Setting a quantity to be batched greater than the scale capacity with automatic calculation of cycles.<br>→ Not available for CE-M approved version.                                                                                                                                                               | OPZWQMC         |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | — • — • • •     |
|  | Intermediate unloadings during the batching.<br>→ Not available for CE-M approved version.                                                                                                                                                                                                                         | OPZWSCARI       |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | — — — • • •     |
|  | Partial unloadings at cycle end.<br>→ Not available for CE-M approved version.                                                                                                                                                                                                                                     | OPZWSCARP       |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | — — — • • •     |
|  | Alibi memory.                                                                                                                                                                                                                                                                                                      | OPZWALIBI       |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | • • • • • •     |
|  | Data transfer from the instrument to the PC, via RS232 (directly) or RS485 (by converter) serial port. These data (weighed values, batchings, alarms) can be imported and processed on the PC using the PROG-DB software included. We suggest to use this option when the indicator is always connected to the PC. | OPZWDATIPC      |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | • • • • • •     |
|  | Manual batching with remote displays connected in parallel to the instrument via RS485 serial port; allows to display on different remote displays the following batching information: formula and product number, remaining quantity to be batched, gross weight.                                                 | OPZWLAUMAN      |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | B C S 3P 6P 14P |
|                                                                                     |                                                                                                                                                                                                                                                                                                                    | — • • • • •     |